

CAT. N° 4 232 28



DPX³250 HP S1 ELECTRONIC RELEASE MCCB FIXED VERSION - BREAKING CAPACITY 50KA - 4P - 250A

Pack (number of units)	1
Volume (dm ³)	4,232
Weight (g)	2 532,00

Product characteristics

MCCBs - fixed version

- Protection against overloads:
 - Ir adjustable from 0.4 to 1 x In
 - tr adjustable from 3 to 15s
- Protection against short circuits:
 - I_{sd} adjustable from 1.5 to 10 x Ir
 - tsd adjustable from 0 to 0.5s

Breaking capacity I_{cu} 50 kA (400 V~)

- 4P
- In : 250 A

General characteristics

DPX³ 250 HP - S1 electronic release MCCBs from 40 to 250 A - fixing on plate

- Moulded case MCCBs for switching, control isolation and protection of low voltage electrical lines
- Can be fitted with auxiliaries
- Supplied with: screws for connection fixing screws, connection plates for bars and cable lugs and insulated shIELDS (phase barriers)
- Can be fitted with cage terminals 120 mm² max. (flexible cable) or 150 mm² max. rigid cable
- Can be mounted on plate in XL³ and XL³ S cabinets and enclosures
- Conform to IEC 60947-2

Documentation

Installation instructions & related documents

- [LE11682AA](#)

Installation & technical data

- [F03044EN00_DPX3250_HPS1_ELEv](#)
- [EXB19026_CA_DPX3_125HP250HP_630_1600E](#)
- N