

CAT. N° 4 232 35



## DPX<sup>3</sup>250 HP S1 ELECTRONIC MCCB WITH ELECTRONIC EARTH LEAKAGE MODULE FIXED VERSION - 50KA - 4P - 40A

Pack (number of units)	O/R
Volume (dm <sup>3</sup> )	O/R
Weight (g)	O/R

### Product characteristics

#### MCCBs with electronic earth leakage module - fixed version

- Protection against overloads:
  - Ir adjustable from 0.4 to 1 x In
  - tr adjustable from 3 to 15s
- Protection against short circuits:
  - lsd adjustable from 1.5 to 10 x Ir
  - tsd adjustable from 0 to 0.5s
- Equipped with earth leakage module with knobs
- Adjustable sensitivity: 0.03 - 0.3 - 1 - 3 A
- Adjustable tripping: 0 - 0.3 - 1 - 3s (with 0.03 A possible only 0s)

#### Breaking capacity Icu 50 kA (400 V~)

- 4P
- In : 40 A

### General characteristics

#### DPX<sup>3</sup> 250 HP - S1 electronic release MCCBs from 40 to 250 A - fixing on plate

- Moulded case MCCBs for switching, control isolation and protection of low voltage electrical lines
- Can be fitted with auxiliaries
- Supplied with: screws for connection fixing screws, connection plates for bars and cable lugs and insulated shileds (phase barriers)
- Can be fitted with cage terminals 120 mm<sup>2</sup> max. (flexible cable) or 150 mm<sup>2</sup> max. rigid cable
- Can be mounted on plate in XL<sup>3</sup> and XL<sup>3</sup> S cabinets and enclosures
- Conform to IEC 60947-2

### Documentation

#### Installation instructions & related documents

- [LE11683AA](#)

#### Installation & technical data

- [F03045EN00\\_DPX3250\\_HPS1\\_ELE\\_RCDv](#)
- [EXB19026\\_CA\\_DPX3\\_125HP250HP\\_630\\_1600E](#)  
N