

CAT. N° 4 232 37



DPX³250 HP S1 ELECTRONIC MCCB WITH ELECTRONIC EARTH LEAKAGE MODULE FIXED VERSION - 50KA - 4P - 160A

Pack (number of units)	O/R
Volume (dm ³)	O/R
Weight (g)	O/R

Product characteristics

MCCBs with electronic earth leakage module - fixed version

- Protection against overloads:
 - Ir adjustable from 0.4 to 1 x In
 - tr adjustable from 3 to 15s
- Protection against short circuits:
 - lsd adjustable from 1.5 to 10 x Ir
 - tsd adjustable from 0 to 0.5s
- Equipped with earth leakage module with knobs
- Adjustable sensitivity: 0.03 - 0.3 - 1 - 3 A
- Adjustable tripping: 0 - 0.3 - 1 - 3s (with 0.03 A possible only 0s)

Breaking capacity Icu 50 kA (400 V~)

- 4P
- In : 160 A

General characteristics

DPX³ 250 HP - S1 electronic release MCCBs from 40 to 250 A - fixing on plate

- Moulded case MCCBs for switching, control isolation and protection of low voltage electrical lines
- Can be fitted with auxiliaries
- Supplied with: screws for connection fixing screws, connection plates for bars and cable lugs and insulated shileds (phase barriers)
- Can be fitted with cage terminals 120 mm² max. (flexible cable) or 150 mm² max. rigid cable
- Can be mounted on plate in XL³ and XL³ S cabinets and enclosures
- Conform to IEC 60947-2

Documentation

- ✂ Installation instructions & related documents
 - [LE11683AA](#)

- 📖 Installation & technical data
 - [F03045EN00_DPX3250_HPS1_ELE_RCDv](#)
 - [EXB19026_CA_DPX3_125HP250HP_630_1600E](#)
N