

CAT. N° 4 236 79



DPX³125 HP THERMAL MAGNETIC MCCB WITH ELECTRONIC EARTH LEAKAGE MODULE FIXED VERSION - 50KA - 4P - 125A

Pack (number of units)	1
Volume (dm ³)	2,338
Weight (g)	1 578,00

Product characteristics

MCCBs with electronic earth leakage module - fixed version

- Thermal adjustable from 0.8 to 1 In
- Magnetic fixed at 10 In (fixed at 400 A for In from 16 A to 40 A)
- Equipped with earth leakage module
- Adjustable sensitivity: 0.03 - 0.3 - 1 - 3 A
- Adjustable tripping: 0 - 0.3 - 1 - 3s (with 0.03 A possible only 0 s)

Breaking capacity Icu 50 kA (400 V~)

- 4P
- In : 125 A

General characteristics

DPX³ 125 HP - thermal magnetic release MCCBs from 16 to 125 A - fixing on plate

- Moulded case MCCBs for switching, control isolation and protection of low voltage electrical lines
- Can be fitted with auxiliaries
- Supplied with: screws for connections, fixing screws and insulated shields (phase barriers)
- Can be fitted with cage terminals 120 mm² max. (flexible cable) or 150 mm² max. rigid cable
- Conform to IEC 60947-2
- Sealable adjustment
- Can be mounted on plate in XL³ and XL³ S cabinets and enclosures

Documentation

Installation instructions & related documents

- [LE11962AA](#)

Environmental product profile

- [LGRP-01416-V01](#)

Installation & technical data

- [F03041EN00_DPX3125_HPTM_RCDv](#)
- [EXB19026_CA_DPX3_125HP250HP_630_1600E](#)
N