

CAT. N° 4 239 06



## DPX<sup>3</sup>250 HP MAGNETIC RELEASE ONLY FOR MOTOR PROTECTION - BREAKING CAPACITY 36KA - 3P - 80A

Pack (number of units)	O/R
Volume (dm <sup>3</sup> )	O/R
Weight (g)	O/R

### Product characteristics

#### DPX<sup>3</sup> 250 HP

- Magnetic adjustable from 6 to 14 In
- Can be mounted on plate in XL<sup>3</sup> and XL<sup>3</sup> S cabinets and enclosures

#### Breaking capacity I<sub>cu</sub> 36 kA (400 V~)

- 3P
- In : 80 A

### General characteristics

#### DPX<sup>3</sup> magnetic release only - MCCBs from 16 to 1250 A for motor protection

- Moulded case MCCBs for switching, control isolation and protection of three-phase motors
- Can be fitted with auxiliaries
- Supplied with: screws for connections, fixing screws and insulated shields (phase barriers)
- Conform to IEC 60947-2

### Documentation

#### Installation instructions & related documents

- [LE12994AA](#)

#### Installation & technical data

- [F03046EN02\\_DPX3250HP\\_OM\\_v](#)
- [EXB19026\\_CA\\_DPX3\\_125HP250HP\\_630\\_1600E](#)
- [N](#)