

CAT. N° 4 239 41



DPX³250 HP MAGNETIC RELEASE ONLY FOR MOTOR PROTECTION - BREAKING CAPACITY 50KA - 4P - 50A

Pack (number of units)	O/R
Volume (dm ³)	O/R
Weight (g)	O/R

Product characteristics

DPX³ 250 HP

- Magnetic adjustable from 6 to 14 In
- Can be mounted on plate in XL³ and XL³ S cabinets and enclosures

Breaking capacity Icu 50 kA (400 V~)

- 4P
- In : 50 A

General characteristics

DPX³ magnetic release only - MCCBs from 16 to 1250 A for motor protection

- Moulded case MCCBs for switching, control isolation and protection of three-phase motors
- Can be fitted with auxiliaries
- Supplied with: screws for connections, fixing screws and insulated shields (phase barriers)
- Conform to IEC 60947-2

Documentation

Installation instructions & related documents

- [LE12994AA](#)

Installation & technical data

- [F03046EN02_DPX3250HP_OM_v](#)
- [EXB19026_CA_DPX3_125HP250HP_630_1600EN](#)