

CAT. N° 4 311 21



## DCX-M CHANGEOVER SWITCHE - SIZE 1 - 3P+N - 63 A - I-O-II

Pack (number of units)	1
Volume (dm <sup>3</sup> )	2,395
Weight (g)	899,00

### Product characteristics

#### Changeover switches

##### Size 1

- Cage terminals
- 3P+N
- Intensity : 63 A
- Handle : I - O - II

### General characteristics

#### DCX-M changeover switches - from 40 to 1600 A

- Conform to IEC EN 60947-3
- Moulded case design with frame parts of non - flammable glass fibre reinforced polyester with high mechanical and electrical track resistance and with low water absorption
- Knife - type contacts with self - wiping action on the contact surfaces, providing:
  - under heavy starting currents or with short - circuit conditions, the contact pressure is increased
  - shock and vibration proof contacts
- Four breaking points per pole with two double - break contacts

### Documentation



#### Catalogue pages & additional information

- [Description page \(p.172\)](#)
- [Selection chart \(p.174-175\)](#)
- [DCX-M changeover switches](#)



#### Installation instructions & related documents

- [4197Z007-Y4512A](#)