

CAT. N° 4 311 31

**DCX-M CHANGEOVER SWITCHE - SIZE 5 - 3P+N - 1000 A - I-O-II**

Pack (number of units)	1
Volume (dm ³)	57,761
Weight (g)	26 177,00

Product characteristics**Changeover switches****Size 5**

- Connection with lugs
- 3P+N
- Intensity : 1000 A
- Handle : I - O - II

General characteristics**DCX-M changeover switches - from 40 to 1600 A**

- Conform to IEC EN 60947-3
- Moulded case design with frame parts of non - flammable glass fibre reinforced polyester with high mechanical and electrical track resistance and with low water absorption
- Knife - type contacts with self - wiping action on the contact surfaces, providing:
 - under heavy starting currents or with short - circuit conditions, the contact pressure is increased
 - shock and vibration proof contacts
- Four breaking points per pole with two double - break contacts

Documentation **Catalogue pages & additional information**

- [Description page \(p.172\)](#)
- [Selection chart \(p.174-175\)](#)
- [DCX-M changeover switches](#)