

CAT. N° 4 460 22



LCS³ 19" SERVER CABINETS WITH AIRFLOW MANAGEMENT - 46U - WIDTH 800 MM AND DEPTH 1100 MM

| | |
|---------------------------|------------|
| Pack (number of units) | 1 |
| Volume (dm ³) | 2388,32 |
| Weight (g) | 127 800,00 |

Product characteristics

LCS³ 19" server cabinets with airflow management

- Capacity: : 46 U
- Width: : 800 mm
- Depth: : 1100 mm

General characteristics

Legrand cabling system LCS³ enclosures - server cabinets and cable entries

- Colour: RAL 9011 (black)
- Frame: aluminium, demountable
- Load capacity: 1500 kg (static)
- 80 % perforated front door and 80 % perforated double rear doors: all doors are fitted with a Fix-easy swivel handle with an EK-333 cylinder lock
- Roof: 3 or 4 cut outs with 2 or 3 blind plates and 1 cable entry brush depending on the frame size
- Interior: cabinet equipped with 4 x 19" profiles including height (U) indication
- Distance to the cabinet front: set to 80 mm (pitch set to 740 mm)
- Cabinet equipped with two cable trays for cable management. Special features include toolless-mounting key holes for mounting vertical PDU's and fixation points to mount Plastic Cable Rings (Cat.No 4 460 57)
- Cabinets supplied with 20 cage nuts and screws
- Server cabinets delivered without side panels. Server cabinets with airflow management are supplied with an airflow management package keeping the loss of air to a minimum, thus improving energy efficiency

Documentation

Catalogue pages & additional information

- [Selection chart \(p.724\)](#)
- [Description page \(p.758\)](#)

Installation & technical data

- [Server-cabinet-with-airflow-package](#)