

CAT. N° 4 464 01



19INCHES SERVER CABINET LCS³ 42U - 600X1200MM

Pack (number of units)	O/R
Volume (dm ³)	O/R
Weight (g)	O/R

Product characteristics

LCS³ 19" server cabinets

- Capacity : 42 U
- Width : 600 mm
- Depth : 1200 mm

General characteristics

Legrand cabling system LCS³ enclosures - server cabinets

- Colour: Black RAL 9005
- Frame: aluminium, demountable
- Load capacity: 1500 kg (static)
- 80 % perforated front door and 80 % perforated double rear doors: all doors are fitted with a Fix-easy swivel handle with a EK333 locking
- Roof: 3 cut-outs (the left and right ones have blindplates and brushes, the center one has a blind plate)
- Interior: cabinet equipped with 4 x 19" profiles including height (U) indication
- Distance to the cabinet with airflow front: set to 80 mm (pitch set to 100 mm). Distance to the cabinet front: set to 175 mm (pitch set to 100 mm)
- Server cabinets supplied without side panels
- Server cabinets with airflow management are supplied with an airflow management package keeping the loss of air to a minimum, thus improving energy efficiency and with a sideskirt with cut-outs and blind panels
- Cabinets equipped with leveling feet

Documentation



Installation & technical data

- [LCS3_SERVERCABINET-TDV02-EN](#)