

CAT. N° 4 464 30



19INCHES CABLING CABINET LCS³ 24U - 800X800X1300MM

Pack (number of units)	1
Volume (dm ³)	895,57
Weight (g)	84 800,00

Product characteristics

LCS³ 19" cabling cabinets - 800 mm wide

- Capacity : 24 U
- Width : 800 mm
- Depth : 800 mm
- Height : 1300 mm

General characteristics

Legrand cabling system LCS³ enclosures - server cabinets

- Colour: Black RAL 9005
- Frame: aluminium, demountable
- Load capacity: 1500 kg (static)
- 80 % perforated front door and 80 % perforated double rear doors: all doors are fitted with a Fix-easy swivel handle with a EK333 locking
- Roof: 3 cut-outs (the left and right ones have blindplates and brushes, the center one has a blind plate)
- Interior: cabinet equipped with 4 x 19" profiles including height (U) indication
- Distance to the cabinet with airflow front: set to 80 mm (pitch set to 100 mm). Distance to the cabinet front: set to 175 mm (pitch set to 100 mm)
- Server cabinets supplied without side panels
- Server cabinets with airflow management are supplied with an airflow management package keeping the loss of air to a minimum, thus improving energy efficiency and with a sideskirt with cut-outs and blind panels
- Cabinets equipped with leveling feet

Documentation



Installation & technical data

- [LCS3_CABLINGCABINET-TDV02-EN](#)