

CAT. N° 4 464 34



## 19INCHES CABLING CABINET LCS<sup>3</sup> 47U - 800X800X2200MM

Pack (number of units)	O/R
Volume (dm <sup>3</sup> )	O/R
Weight (g)	O/R

### Product characteristics

#### LCS<sup>3</sup> 19" cabling cabinets - 800 mm wide

- Capacity : 47 U
- Width : 800 mm
- Depth : 800 mm
- Height : 2200 mm

### General characteristics

#### Legrand cabling system LCS<sup>3</sup> enclosures - cabling cabinets

- Colour: Black RAL 9005
- Frame: aluminium, demountable
- Load capacity: 1500 kg (static)
- Glass front door and blind steel door in the back: all doors are fitted with a Fix-easy swivel handle with a EK333 locking
- Roof: 3 cut-outs (the left and right ones have blind plates and brushes, the center one has a blind plate)
- Interior: cabinet equipped with 4 x 19" profiles including height (U) indication
- Distance to the cabinet front: set to 175 mm (pitch set to 100 mm)
- Cabinets delivered with side panels
- Cabinets equipped with leveling feet

### Documentation



#### Installation & technical data

- [LCS3\\_CABLINGCABINET-TDV02-EN](#)