

CAT. N° 5 551 60



P 17 TEMPRA PRO IP 44 3P+E SURFACE MOUNTING SOCKET LV 16 A WITH FEMALE CONNECTOR - 440 TO 460 V~ - 50/60 HZ

Pack (number of units)	5
Volume (dm ³)	11,672
Weight (g)	1 751,00

Product characteristics

Surface mounting sockets

- Two possible angles (5° or 25°)

440/460 V~

- IP 44
- 16 A
- 3P+E

General characteristics

P 17 Tempra Pro IP 44 - LV 16 and 32 A - sockets, plugs, mobile sockets, appliance inlets and interlocked switched sockets

Documentation

Catalogue pages & additional information

- [Selection chart \(p.380\)](#)

Installation & technical data

- [F01811EN-03](#)

Installation instructions & related documents

- [LE05815AA-01](#)

Agreements & certificates of conformity

- [OC / CB - FR_710665](#)
- [IMQ - CA02_05950](#)
- [CCC - CQC2016010203837679](#)