

CAT. N° 5 552 18

MOBILE SOCKET P17 - IP44 - 380/415 V~ - 32 A - 3P+E


Pack (number of units)	10
Volume (dm ³)	9,923
Weight (g)	2 464,00

Product characteristics
Mobile sockets

- Cable clamping and closing without screws
- Supplied unlocked

380/415 V~

- IP 44
- 32 A
- 3P+E

General characteristics

P 17 Tempra Pro IP 44 - LV 16 and 32 A - sockets, plugs, mobile sockets, appliance inlets and interlocked switched sockets

Documentation

Catalogue pages & additional information

- [Selection chart \(p.380\)](#)
- [Description page \(p.382\)](#)
- [P 17 Tempra Pro](#)


Installation & technical data

- [F01811EN-03](#)


Installation instructions & related documents

- [LE05815AA-01](#)


Agreements & certificates of conformity

- [OC / CB - FR_710665](#)
- [CQC - CQC2016010203850866](#)
- [IMQ - CA02.05952](#)