

CAT. N° 5 552 20

**P 17 TEMPRA PRO IP 44 3P+E MOBILE SOCKET LV 32 A WITH FEMALE CONNECTOR - 440 TO 460 V~ - 50/60 HZ**

Pack (number of units)	5
Volume (dm ³)	7,812
Weight (g)	1 321,00

Product characteristics**Mobile sockets**

- Cable clamping and closing without screws
- Supplied unlocked

440/460 V~

- IP 44
- 32 A
- 3P+E

General characteristics

P 17 Temptra Pro IP 44 - LV 16 and 32 A - sockets, plugs, mobile sockets, appliance inlets and interlocked switched sockets

Documentation **Catalogue pages & additional information**

- [Selection chart \(p.380\)](#)

 **Installation & technical data**

- [F01811EN-03](#)

 **Installation instructions & related documents**

- [LE05815AA-01](#)

 **Agreements & certificates of conformity**

- [OC / CB - FR_710665](#)
- [CQC - CQC2016010203850866](#)
- [IMQ - CA02.05952](#)