

CAT. N° 5 553 05

**MOBILE SOCKET P17 - IP66/67 - 200/250 V~ - 16 A - 3P+E**



Pack (number of units)	5
Volume (dm <sup>3</sup> )	6,391
Weight (g)	1 118,00

**Product characteristics**
**Mobile sockets**

- Supplied unlocked

**200/250 V~**

- 16 A
- 3P+E

**General characteristics**
**P 17 Tempra Pro IP 66/67 LV 16 and 32 A**
**Documentation**
 **Catalogue pages & additional information**

- [Selection chart \(p.381\)](#)
- [Description page \(p.384\)](#)
- [P 17 Tempra Pro](#)

 **Installation & technical data**

- [F01811EN-03](#)

 **Environmental product profile**

- [LGRP-2014-110-V1-EN](#)

 **Installation instructions & related documents**

- [LE05815AA-01](#)

 **Agreements & certificates of conformity**

- [OC / CB-FR\\_710665](#)
- [IMQ-CA02](#)
- [CQC-CQC2016010203850867](#)