

CAT. N° 5 553 55


SURFACE MOUNTING SOCKET P17 - IP66/67 - 200/250 V~ - 16 A - 3P+E


Pack (number of units)	5
Volume (dm ³)	11,672
Weight (g)	1 873,00

Product characteristics
Surface mounting sockets

- Two possible angles (5° or 25°)

200/250 V~

- 16 A
- 3P+E

General characteristics
P 17 Tempra Pro IP 66/67 LV 16 and 32 A
Documentation
 **Catalogue pages & additional information**

- [Selection chart \(p.381\)](#)
- [Description page \(p.384\)](#)
- [P 17 Tempra Pro](#)

 **Installation & technical data**

- [F01811EN-03](#)

 **Environmental product profile**

- [LGRP-2014-112-V1-EN](#)

 **Installation instructions & related documents**

- [LE05815AA-01](#)

 **Agreements & certificates of conformity**

- [QC / CB-FR_710665](#)
- [IMQ-CA02](#)
- [CCC-CQC2016010203837679](#)