

REF . 5 554 54

**SURFACE MOUNTING SOCKET P17 - IP66/67 - 200/250 V~ - 32 A - 2P+E**

Emballage (nombre number of units)	5
Volume (dm ³)	18,673
Poids (g)	2 591,00

Caractéristiques du produit**Surface mounting sockets**

- Two possible angles (5° or 25°)

200/250 V~

- 32 A
- 2P+E

Caractéristiques générales**P 17 Tempra Pro IP 66/67 LV 16 and 32 A****Documentation associée****Catalogue pages & additional information**

- [Selection chart \(p.381\)](#)
- [Description page \(p.384\)](#)
- [P 17 Tempra Pro](#)

**Installation & technical data**

- [F01811EN-03](#)

**Environmental product profile**

- [LGRP-2014-112-V1-EN](#)

**Installation instructions & related documents**

- [LE05815AA-01](#)

**Agreements & certificates of conformity**

- [IMQ-CA02](#)
- [OC / CB-FR_710665](#)