

CAT. N° 5 554 56



SURFACE MOUNTING SOCKET P17 - IP66/67 - 200/250 V~ - 32 A - 3P+N+E

Pack (number of units)	5
Volume (dm ³)	18,673
Weight (g)	2 839,00

Product characteristics

Surface mounting sockets

- Two possible angles (5° or 25°)

200/250 V~

- 32 A
- 3P+N+E

General characteristics

P 17 Tempra Pro IP 66/67 LV 16 and 32 A

Documentation

Catalogue pages & additional information

- [Selection chart \(p.381\)](#)
- [Description page \(p.384\)](#)
- [P 17 Tempra Pro](#)

Installation & technical data

- [F01811EN-03](#)

Environmental product profile

- [LGRP-2014-112-V1-EN](#)

Installation instructions & related documents

- [LE05815AA-01](#)

Agreements & certificates of conformity

- [IMQ-CA02](#)
- [OC / CB-FR_710665](#)