

CAT. N° 5 555 19


APPLIANCE INLET P17 PRO - IP66/67 - 200/250 V~ - 63 A - 3P+N+E


Pack (number of units)	2
Volume (dm ³)	20,874
Weight (g)	3 500,00

Product characteristics
Appliance inlets
380/415 V~

- 63 A
- 3P+N+E

General characteristics
P 17 Tempra Pro IP 66/67 LV 63 and 125 A
Documentation
 **Catalogue pages & additional information**

- [Selection chart \(p.381\)](#)
- [Description page \(p.385\)](#)
- [P 17 Tempra Pro](#)

 **Installation & technical data**

- [F02385EN-01](#)

 **Installation instructions & related documents**

- [LE05815AA-01](#)

 **Agreements & certificates of conformity**

- [OC / CB-FR_706516](#)