

REF . 5 556 08

**MOBILE SOCKET P17 PRO - IP66/67 - 380/415 V~ - 125 A - 3P+E**

Emballage (nombre number of units)	1
Volume (dm ³)	7,88
Poids (g)	1 545,00

Caractéristiques du produit**Mobile sockets****380/415 V~**

- 125 A
- 3P+E

Caractéristiques générales**P 17 Tempra Pro IP 66/67 LV 63 and 125 A****Documentation associée** **Catalogue pages & additional information**

- [Selection chart \(p.381\)](#)

 **Installation & technical data**

- [F02385EN-01](#)

 **Environmental product profile**

- [LGRP-00206-V01](#)

 **Installation instructions & related documents**

- [LE05815AA-01](#)

 **Agreements & certificates of conformity**

- [OC / CB-FR_706516](#)
- [CCC-CQC2018010203055870](#)