

CAT. N° 5 720 76



## WIRELESS POWER CHARGER 1 A - 5 V/5 W + TYPE-A 2.4 A / 12 W USB CHARGING PORT ARTEOR - 2 MODULES - WHITE

Pack (number of units)	1
Volume (dm <sup>3</sup> )	1,516
Weight (g)	184,00

### Product characteristics

#### Wireless charger + Type-A USB - Arteor version

- 1 A - 5 V/5 W charger with one 3 A/12 W USB port to power a second device
- Specially designed for work areas
- For installation in flush-mounting box, surface mounting box, workstation kit, column module, multioutlet extension for offices, etc
- To be fitted with a support and a plate depending on the selection of the wiring accessories ranges
- Comes with 2 induction antennae for fast intuitive smartphone charging
- Recognition area: 50 x 80 mm
- Plate at an angle of 10° with non-slip coating to hold the terminal safely in place during charging
- Dimensions: 136.5 x 70 x 56.5 mm
- Anti-theft lock function
- Can be mounted in multiple horizontal positions
- White with metallic finishing plate
- 2 x 2.5 mm<sup>2</sup> terminals

### General characteristics

#### Arteor™ wireless power chargers

- Wireless power chargers for fast charging a smartphone with a Qi receiver
- Power supply standby mode consumption
- Conform to the Qi WPC standard (Wireless Power Consortium): certified for professional Qi 1.2.3 projects
- Conform to EN 62479 standard (EMF emissions)
- Conform to ICNIRP specifications (health protection)
- Do not interfere with other wireless signals (Zigbee, TNT, GSM, 4G, etc)

### Documentation

#### Catalogue pages & additional information

- [Description page \(p.461\)](#)

#### Installation & technical data

- [F02380EN-00](#)

#### Installation instructions & related documents

- [LE09623AC](#)
- [LE09623AB](#)