

REF . 5 722 57



READING LIGHT ARTEOR - SQUARE VERSION - 2 MODULES - WHITE



Emballage (nombre number of units)	1
Volume (dm ³)	1,216
Poids (g)	156,00

Caractéristiques du produit

Reading lights

- Fitted with maintenance-free LEDs
- LED colours: 3000 K (neutral white)
- 230 V power supply - energy class A
- Screw terminals
- For installation in the bedhead. Offers directional lighting
- Equipped with a flexible cable so the head can swivel
- Built-in dimmer. Consumption 3.3 W
- Luminous flux 110 lumen (equivalent to 15 W incandescent). Service life 40000 hours
- For installation in box depth 40 mm min.
- 2 modules

Square version

- White

Caractéristiques générales

Arteor™ visual indication

- Mechanisms supplied with rocker plates, to be equipped with support frames and plates

Documentation associée

Catalogue pages & additional information

- [Description page \(p.440\)](#)
- [Description page \(p.458\)](#)

Installation & technical data

- [F02054EN-00](#)

Installation instructions & related documents

- [LE08219AA](#)

Agreements & certificates of conformity

- [OC / CB-700842](#)