

REF . 5 726 91

**TV SOCKET ARTEOR - TV-R-SAT SHIELDED - 0-2400 HZ - 2
MODULES - CHAMPAGNE**

| | |
|-------------------------------------|-----|
| Emballage (nombre number of units) | O/R |
| Volume (dm ³) | O/R |
| Poids (g) | O/R |

Caractéristiques du produit**Multi TV star sockets**

- 2 modules

TV-R-SAT sockets

- Low attenuation: 1.5 dB
- Can be installed in receptacles for floor sockets
- Champagne

Caractéristiques générales**Arteor™ television sockets**

- Mechanisms supplied with rocker plates, to be equipped with support frames and plates
- For Dvbt, Cablecast and satellite installation
- UHD TV quality compatible
- Classe A shielded star socket LTE ready (4G protected)
- Recommended coaxial cable: 17 VATCA
- Star cabling (1 socket = 1 cable to antenna, splitter or multiswitch). Visual check of the connection
- Meets EN 50083-4 and EN 50083-2 European directive
- TV: male connector (Ø9.5 mm) - 5-68 /120-862 MHz
- R: female connector (Ø9.5 mm) - 87.5-108 MHz
- SAT: "F" type connector - 950-2400MHz

Documentation associée**Installation & technical data**

- [F00842EN-02](#)