

CAT. N° 5 728 45



RJ45 SOCKET ARTEOR - CATEGORY 6A STP - 1 MODULE - SOFT ALU

Pack (number of units)	O/R
Volume (dm ³)	O/R
Weight (g)	O/R

Product characteristics

Cat. 6A sockets

- 360° metal shielding

STP - 1 module

- Soft Alu

General characteristics

Arteor™ RJ 45 sockets

- With LCS² connector with fast connection thanks to integrated crimping
- Take AWG 22 single-core cables up to AWG 26 and AWG multicore cables
- Contacts marked with dual colour code and wiring schemes T568 A and T 568 B
- Conform to standards ISO/IEC 11801 Ed. 2.0, amendment 2, EN 50173-1 and TIA/EIA 568 C
- Mechanisms supplied with rocker plates, to be equipped with support frames and plates

Documentation

Agreements & certificates of conformity

- [AoC-PL2_Cat6A_FFTP_32799_ac1171009](#)
- [AoC-CL2_Cat6A_FFTP_32799_ac1171010](#)
- [AoC-PL2_Cat6A_FTP_32778_ac1171014](#)
- [AoC-CL2_Cat6A_STP_32777_ac1171018A](#)
- [AoC-PL3_Cat6A_FTP_32778_ac1171016](#)
- [AoC-CL2_Cat6A_FTP_32778_ac1171015](#)
- [AoC-PL3_Cat6A_STP_32777_ac1171019A](#)
- [AoC-PL2_Cat6A_STP_32777_ac1171017A](#)
- [AoC-CL4_Cat6A_STP_32869_ac1181045](#)
- [AoC-CL4_Cat6A_STP_32778_ac1181044](#)
- [AoC-PL2_C6A_FFTP_32883_ac1191060](#)
- [AoC-CL2_C6A_FFTP_32883_ac1191061](#)
- [AoC-PL2_C6A_UFTP_32884_ac1191058](#)
- [AoC-CL2_C6A_STP_32882_ac1191063](#)
- [AoC-4PPoE_2019-676_Ac_Delta_Force](#)
- [AoC-CL2_C6A_UFTP_32884_ac1191059](#)
- [AoC-PL3_Cat6A_FFTP_32799_ac1171011](#)
- [AoC-PL2_C6A_STP_32882_ac1191062](#)