

CAT. N° 5 740 55

**MOTION SENSOR ARTEOR 3-WIRE WITH NEUTRAL 400 W  
- 2 MODULES - MAGNESIUM**

Pack (number of units)	1
Volume (dm <sup>3</sup> )	0,235
Weight (g)	69,00

**Product characteristics****Motion sensors**


- Measurement of luminosity threshold
- Adjustment of luminosity threshold and time delay
- Max. lux and min. time delay factory pre-set
- Recommended fixing height: 1 m
- IR detection 180°
- Adjustable luminosity threshold: 5 to 1275 lux
- Installation in box min. depth 40 mm recommended
- 2 modules
- Range 8 m

**With neutral, 3-wire - 400 W**

- Only 1 motion sensor per lighting circuit
- No possibility to add a push button to control also the lighting circuit
- Time delay adjustable from 10 s to 10 min
- Consumption 0.55 W on standby
- Magnesium

**General characteristics****Arteor™ motion sensors**

- Mechanisms supplied with rocker plates, to be equipped with support frames and plates

**Documentation** **Catalogue pages & additional information**

- [Description page \(p.455\)](#)
- [Technical page \(p.457\)](#)

 **Installation instructions & related documents**

- [LE09856AA](#)