

REF . 6 019 98

**CABINETS PLE XO<sup>3</sup> - IP65 - IK09 - 8 MODULES - 1 ROW**

Emballage (nombre number of units )	6
Volume (dm <sup>3</sup> )	32,852
Poids (g)	4 550,00

**Caractéristiques du produit****Cabinets 2 to 8 modules**

- Number of rows : 1
- Number of modules : 8

**Caractéristiques générales****Plexo<sup>3</sup> - IP 65 weatherproof cabinets, multifunction sleeves and accessories**

- Self-extinguishing: resistance to incandescent wire 650°C.
- Allows to achieve assemblies conform to IEC 61 439 - 3
- Weatherproof cabinets - IP 65 - IK 09 - Class II
- Door and cabinet fully reversible. Removable chassis and faceplates from 2-row versions up
- 2-position rail for modular products and moulded cases. Spacing between rails 150 mm
- Can be fitted with perforated plates and solid faceplates for mounting non-modular products
- Lockable door handle, sealable cover and faceplate
- Shock-resistant polystyrene material
- Box colour light grey L750A, cover colour dark grey R746A
- Supplied without terminal blocks

**Documentation associée** **Catalogue pages & additional information**

- [Description page \(p.286\)](#)
- [Technical page \(p.287\)](#)

 **Agreements & certificates of conformity**

- [QC / CB-654748](#)
- [LOVAG-IT 17](#)

 **Installation & technical data**

- [F01043EN02](#)
- [EXB14046\\_CA\\_Plexo3\\_EN\\_print](#)