

CAT. N° 6 027 98

IP41 KIT FOR XL³-N 250 DISTRIBUTION BOARDS

Pack (number of units)	O/R
Volume (dm ³)	O/R
Weight (g)	O/R

Product characteristics

Accessories

IP 41 kit

- For XL³-N 250 distribution boards

General characteristics

XL³-N 250 3-phase distribution boards - from 12 to 54 poles (outgoing terminals)

- 3-phase distribution boards for DIN-rail mounting circuit breakers; IP 40 (IP 41 with the kit Cat.No 6 027 98) - IK 08 with door
- Conform to standard IEC 61439-2; Type tested; tested and certified by third part laboratory
- Maximum voltage 480 V~; Rated short-time withstand current (I_{cs}): 17 kA 0.2 s; Rated peak withstand current (I_{pk}): 34 kA
- Ambient temperature: 50 °C continuously
- Zinc coated metal; Grey RAL 7035
- Supplied with: surface or flush-mounting box, reversible door with handle, faceplate, fully isolated tin plated copper busbar
- The number of holes of earth and neutral terminal blocks are equal to the number of outgoing devices

Documentation



Catalogue pages & additional information

- [Description page \(p.210\)](#)
- [Technical page \(p.211\)](#)