

CAT. N° 6 044 32



## CONVIVIO DISTRIBUTION BOARD - 24 OUTGOING TERMINALS - MAX. 125 A - WITH MOUNTING PLATE FOR MAIN CIRCUIT BREAKER

Pack (number of units)	O/R
Volume (dm <sup>3</sup> )	O/R
Weight (g)	O/R

### Product characteristics

#### Distribution boards up to 250 A

##### Maximum rating 125 A

- Flush or surface mounting
- Equipped with mounting plate for main circuit breaker: DRX 125 MCCB
- Number of poles : 24 outgoing terminals
- No of 3P ways : 8

### General characteristics

#### Convivio™ 3-phase distribution boards - from 12 to 54 poles (outgoing terminals)

- 3-phase distribution boards for DIN-rail mounting circuit breakers
- IP 40 - IK 08 with door
- Conform to standard IEC 61439-3: busbar type tested (Lovag certified)
- Maximum voltage 480 V~; Rated short-time withstand current (I<sub>cs</sub>): 17 kA 0.2 s
- Rated peak withstand current (I<sub>pk</sub>): 34 kA
- Ambient temperature: 50 °C continuously
- White RAL 9003
- Supplied with: surface or flush-mounting box, door with handle, faceplate, fully isolated tin plated copper busbar
- The number of holes of earth and neutral terminal blocks are equal to the number of outgoing devices

### Documentation

#### Catalogue pages & additional information

- [Description page \(p.208\)](#)
- [Technical page \(p.209\)](#)

#### Installation & technical data

- [F02538EN-01](#)

#### Installation instructions & related documents

- [LE07122BB](#)