

CAT. N° 6 045 60



EXTENSION BOX TO BE INSTALLED ON XL³-N 630 DISTRIBUTION BOARDS WIDTH 710 MM AND DEPTH 175 MM

Pack (number of units)	O/R
Volume (dm ³)	O/R
Weight (g)	O/R

Product characteristics

Extension boxes

- To be installed on XL³-N 630 distribution boards (at the top or at the bottom) for extra wiring space or additional functions.
- For XL³-N 630 width : 710 mm
- For XL³-N 630 depth : 175 mm

General characteristics

XL³-N 630 3-phase distribution boards - from 12 to 54 poles (outgoing terminals)

- 3-phase distribution boards for moulded case circuit breakers, DRX or DPX³; IP 40 (IP 42 with the kit Cat.No 6 045 68) - IK 08 with door
- Conform to standard IEC 61439-2.Type tested; tested and certified by third part laboratory; Maximum voltage 415 V-
- Rated peak withstand current (Ipk): up to 110 kA
- Ambient temperature: 50 °C continuously; Grey RAL 7035;
- Supplied with: surface mounting box, door with handle, faceplate, fully isolated tin plated copper busbar
- The number of holes of earth and neutral terminal blocks are equal to the number of outgoing devices

Documentation

Catalogue pages & additional information

- [Description page \(p.213\)](#)