

CAT. N° 6 170 01



## SINGLE POLE SWITCH BELANKO - 1 GANG - 2-WAY - 10 AX 250 V~ - LARGE ROCKER

|                           |        |
|---------------------------|--------|
| Pack (number of units)    | 10     |
| Volume (dm <sup>3</sup> ) | 3,264  |
| Weight (g)                | 697,00 |

### Product characteristics

#### Single pole switches 10 AX - 250 V~

- Conform to BS EN 60669-1

#### Large rocker

- 1 gang - 2-way switch

### General characteristics

#### Belanko™ - single pole switches and push-buttons

- Colour: White T084
- Material: Thermoplastic with glossy finish
- Dimensions: 86 x 86 x 9.5 mm (1 gang) / 86 x 146 x 9.5 mm (2 gang)
- Supplied with 2 screws M3.5 for BS boxes

### Documentation

#### Catalogue pages & additional information

- [Description page \(p.548\)](#)

#### Agreements & certificates of conformity

- [OC / CB-CN51288](#)
- [OC / CB-CN51288-A1/M1](#)

#### Installation & technical data

- [F01046EN-02](#)

#### Environmental product profile

- [LGRP-00134-V01](#)