

CAT. N° 6 170 30



ROTARY DIMMER BELANKO - 600 W230 V - 1 GANG - 1 WAY

Pack (number of units)	1
Volume (dm ³)	0,608
Weight (g)	127,00

Product characteristics

Dimmers

600 W R dimmer (230 V only)

- Rotary on/off dimmer - 50 Hz
- 1 gang – 1-way
- 40-600 W (230 V) for incandescent and halogen lamps

General characteristics

Belanko™ - dimmers and ventilation control

- Colour: White T084
- Material: Thermoplastic with glossy finish
- Dimensions: 86 x 86 x 9.5 mm (1 gang) / 86 x 146 x 9.5 mm (2 gang)
- Supplied with 2 screws M3.5 for BS boxes

Documentation

Catalogue pages & additional information

- [Description page \(p.549\)](#)
- [Belanko™ - dimmers and ventilation control](#)

Agreements & certificates of conformity

- [I.R.-](#)

Installation & technical data

- [F01049EN-02](#)