

CAT. N° 6 170 48

**BS SOCKET OUTLET BELANKO - 2 GANG DOUBLE POLE SWITCHED - 13 A 250 V~**

Pack (number of units)	5
Volume (dm ³)	3,264
Weight (g)	1 123,00

Product characteristics**Belanko**

- White

2P+E - 13 A - double pole switched

- 2 gang double pole switched

General characteristics**Rigid cover DLP-S universal trunking - British standard socket outlets**

- To be used with universal support for British standard wiring accessories Cat.No 6 380 05

Documentation **Catalogue pages & additional information**

- [Description page \(p.551\)](#)
- [Selection chart \(p.834-835\)](#)
- [Rigid cover DLP-S snap-on and universal trunking](#)

 **Agreements & certificates of conformity**

- [QC / CB-CN48796-A1/M2](#)
- [G-MARK-LVE/2020/000913 v2](#)

 **Installation & technical data**

- [F01053EN-01](#)