

REF . 6 170 58



**BRITISH STANDARD SOCKET OUTLET BELANKO WITH  
USB TYPE A CHARGER - 1 GANG SINGLE POLE SWITCHED  
- 13 A 250 V~**



Emballage (nombre number of units )	1
Volume (dm <sup>3</sup> )	0,426
Poids (g)	125,00

### Caractéristiques du produit

**British Standard socket outlets - 13 A- 250 V~ with USB charger**

- Conform to BS 1363-2:2016
- Conform to IEC 60950-1

**1 gang**


- USB Type-A 2.4 A - 5 VDC - 12 W
- Consumption in passive mode less than 0.08 W
- 1 gang single pole switched

### Caractéristiques générales

**Belanko™ - socket outlets**

- Colour: White T084
- Material: Thermoplastic with glossy finish
- Dimensions: 86 x 86 x 9.5 mm (1 gang) / 86 x 146 x 9.5 mm (2 gang)
- Supplied with 2 screws M3.5 for BS boxes

### Documentation associée

 **Catalogue pages & additional information**

- [Description page \(p.551\)](#)

 **Agreements & certificates of conformity**

- [OC / CB-C-63 SE-88179M2](#)
- [OC / CB-FR-708240/M1](#)
- [OC / CB-SE-104797](#)
- [OC / CB-SE-86037](#)
- [OC / CB-SE-101858](#)
- [OC / CB-SE-86037M1](#)
- [G-MARK-0048202100027/A1](#)

 **Installation & technical data**

- [F02764EN-00](#)