

CAT. N° 6 170 60

**EURO/US SOCKET OUTLET BELANKO - 1 GANG - 2P - 16 A
250 V~ / 15 A - 127 V~**

Pack (number of units)	10
Volume (dm ³)	2,949
Weight (g)	755,00

Product characteristics**Euro/US standard socket outlets - 16 A - 250 V~ / 15 A - 127 V~**

- 1 gang - 2P

General characteristics**Belanko™ - socket outlets**

- Colour: White T084
- Material: Thermoplastic with glossy finish
- Dimensions: 86 x 86 x 9.5 mm (1 gang) / 86 x 146 x 9.5 mm (2 gang)
- Supplied with 2 screws M3.5 for BS boxes

Documentation**Catalogue pages & additional information**

- [Description page \(p.552\)](#)

**Installation & technical data**

- [F01050EN-02](#)