

CAT. N° 6 170 68


**SHAVER SOCKET BELANKO - 115/230 V - 2 GANG**


Pack (number of units)	1
Volume (dm <sup>3</sup> )	2,177
Weight (g)	708,00

**Product characteristics**
**Shaver socket**

- Conform to BS 61558
- 115/230 V - 20 VA - 50/60 Hz
- Surface or flush-mounting, back box to be min. 47 mm deep - 2 gang

**General characteristics**
**Belanko™ - hotel equipment**

- Colour: White T084
- Material: Thermoplastic with glossy finish
- Dimensions: 86 x 86 x 9.5 mm (1 gang) / 86 x 146 x 9.5 mm (2 gang)
- Supplied with 2 screws M3.5 for BS boxes

**Documentation**
 **Catalogue pages & additional information**

- [Description page \(p.550\)](#)

 **Agreements & certificates of conformity**

- [OC / CB - SG ITS-19496](#)
- [OC / CB - SG ITS-12912](#)

 **Installation & technical data**

- [F01055EN-01](#)