

CAT. N° 6 171 46



BS SOCKET OUTLET BELANKO - 2 GANG SINGLE POLE SWITCHED INBOARD ROCKERS - 13 A 250 V~

Pack (number of units)	5
Volume (dm ³)	2,949
Weight (g)	788,00

Product characteristics

Belanko

- White

2P+E - 13 A - single pole switched

- 2 gang single pole switched with inboard rockers

General characteristics

Rigid cover DLP-S universal trunking - British standard socket outlets

- To be used with universal support for British standard wiring accessories Cat.No 6 380 05

Documentation

Catalogue pages & additional information

- [Description page \(p.551\)](#)
- [Selection chart \(p.834-835\)](#)
- [Rigid cover DLP-S snap-on and universal trunking](#)

Agreements & certificates of conformity

- [OC / CB-SE-105240](#)
- [OC / CB-CN48885](#)
- [OC / CB-CN48885-M1](#)
- [OC / CB-SE-90908](#)
- [OC / CB-SE-90908M1](#)
- [G-MARK-CN-GSOG-20190708R2](#)

Installation & technical data

- [F01053EN-01](#)

Environmental product profile

- [LGRP-00490-V01](#)