

CAT. N° 6 173 35



## DIMMER BELANKO COLOURS - 300 W RLC+LED - DARK GREY

Pack (number of units)	1
Volume (dm <sup>3</sup> )	0,602
Weight (g)	155,00

### Product characteristics

#### Dimmers

##### 300 W RLC+LED dimmer

- For all types of lamps:
  - dimmable LEDs: 5 W to 75 W (10 lamps max. 5 W to 37 W (127 V))
  - dimmable compact fluorescent lamps: 5 W to 75 W (10 lamps max. 5 W to 37 W (127 V))
  - halogen with ferromagnetic or electronic transformer: 5 VA to 300 VA / 5 VA to 150 VA (127 V)
  - fluorescent tube - ballast: 5 VA to 300 VA / 5 VA to 150 VA (127 V)
  - halogen and incandescent 240 VA: 5 W to 300 W / 5 W to 150 W (127 V)
- When switched on, gradually (2 seconds) lights up at the level set before last switch-off
- Dark grey

### General characteristics

#### Belanko™ colours - Dimmers

- Material: Thermoplastic with glossy satin finish
- Dimensions: 86 x 86 x 9.5 mm (1 gang) / 86 x 146 x 9.5 mm (2 gang)
- Supplied with 2 screws M3.5 for BS boxes

### Documentation

#### Catalogue pages & additional information

- [Description page \(p.555\)](#)

#### Agreements & certificates of conformity

- [OC / CB-SE-85949M1](#)
- [OC / CB-SE-85949A1M1](#)
- [OC / CB-SE-85949](#)

#### Installation & technical data

- [F02317EN-01](#)

### PRODUCT INFORMATION



Available until stock lasts