

CAT. N° 6 173 58



BRITISH STANDARD SOCKET OUTLET WITH USB CHARGER BELANKO COLOURS - 1 GANG SINGLE POLE SWITCHED - 13 A 250 V~ - DARK GREY

Pack (number of units)	1
Volume (dm ³)	0,426
Weight (g)	125,00

Product characteristics

British Standard socket outlets 13 A - 250 V~ with USB charger

- Conform to BS 1363-2:2016
- Conform to IEC 60950-1

1 gang single pole switched

- USB Type-A 2.4 A - 5 VDC - 12 W
- Consumption in passive mode less than 0.08 W
- Dark grey

General characteristics

Belanko™ colours - socket outlets

- Material: Thermoplastic with paint satin finish
- Dimensions: 86 x 86 x 9.5 mm (1 gang) / 86 x 146 x 9.5 mm (2 gang)
- Supplied with 2 screws M3.5 for BS boxes

Documentation

Catalogue pages & additional information

- [Description page \(p.557\)](#)

Agreements & certificates of conformity

- [OC / CB-C-63 SE-88179M2](#)
- [OC / CB-FR-708240/M1](#)
- [OC / CB-SE-104797](#)
- [OC / CB-SE-86037](#)
- [OC / CB-SE-101858](#)
- [OC / CB-SE-86037M1](#)
- [G-MARK-0048202100027/A1](#)
- [G-MARK-0048202100027/M1](#)

Installation & technical data

- [F02764EN-00](#)