

CAT. N° 6 173 59



**MULTISTANDARD SWITCHED SOCKET OUTLET WITH USB CHARGER BELANKO COLOURS - 1 GANG -2P+E -16 A 250 V~/15 A 127 V~ -DARK GREY**

|                           |        |
|---------------------------|--------|
| Pack (number of units)    | 1      |
| Volume (dm <sup>3</sup> ) | 0,426  |
| Weight (g)                | 130,00 |

### Product characteristics

**Multistandard switched socket outlets 16 A 250 V~ / 15 A - 127 V~ with USB charger**

- Shuttered for child safety
- USB charger conform to IEC 60950-1

**1 gang - 2P+E**

- USB Type-A 2.4 A - 5 VDC - 12 W
- Consumption in passive mode less than 0.08 W
- Dark grey

### General characteristics

**Belanko™ colours - socket outlets**

- Material: Thermoplastic with paint satin finish
- Dimensions: 86 x 86 x 9.5 mm (1 gang) / 86 x 146 x 9.5 mm (2 gang)
- Supplied with 2 screws M3.5 for BS boxes

### Documentation



**Catalogue pages & additional information**

- [Description page \(p.558\)](#)



**Installation & technical data**

- [F02763EN-00](#)