

CAT. N° 6 177 44



BRITISH STANDARD SOCKET OUTLET WITH USB TYPE-A+C CHARGERS BELANKO S - 13A 250V~ 2 GANG SINGLE POLE SWITCHED - ANTHRACITE

Pack (number of units)	1
Volume (dm ³)	0,991
Weight (g)	204,00

Product characteristics

British Standard socket outlets 13 A - 250 V~ with USB charger

- Conform to BS 1363-2:2016
- Conform to IEC 60950-1

2 gang single pole switched

- USB A-Type + C-Type 3 A - 5 V= 15 W
- Consumption in passive mode
- Anthracite

General characteristics

Belanko™ S - socket outlets

- Material: Thermoplastic with glossy finish
- Dimensions: 86 x 86 x 9.5mm (1 gang) / 86 x 146 x 9.5mm (2 gang)
- Supplied with 2 screws M3.5 for BS boxes

Documentation

 **Installation & technical data**

- [F02982EN-01](#)

 **Agreements & certificates of conformity**

- [OC / CB-SE-102292](#)
- [OC / CB-SE-104641](#)
- [G-MARK-0048202100032/A1](#)
- [G-MARK-0048202100032/M1](#)