

CAT. N° 6 177 57



## BRITISH STANDARD SOCKET OUTLET WITH USB TYPE-A CHARGER BELANKO S - 13A 250V~ 1 GANG UNSWITCHED - ANTHRACITE

Pack (number of units)	O/R
Volume (dm <sup>3</sup> )	O/R
Weight (g)	O/R

### Product characteristics

#### British Standard socket outlets 13 A - 250 V~ with USB charger

- Conform to BS 1363-2:2016
- Conform to IEC 60950-1

#### 1 gang unswitched

- USB A-Type 2.4 A - 5 V= - 12 W
- Consumption in passive mode
- Anthracite

### General characteristics

#### Belanko™ S - socket outlets

- Material: Thermoplastic with glossy finish
- Dimensions: 86 x 86 x 9.5mm (1 gang) / 86 x 146 x 9.5mm (2 gang)
- Supplied with 2 screws M3.5 for BS boxes

### Documentation

#### Installation & technical data

- [F02982EN-01](#)

#### Agreements & certificates of conformity

- [OC / CB-SE-104796](#)
- [OC / CB-SE-101851](#)
- [G-MARK-0048202100029/M1](#)