

CAT. N° 6 462 02



LINKEO FIX 19" CABINET WITH FIX SIDE PANELS - CAPACITY 12U - DIMENSIONS 625X600X450 MM - READY-ASSEMBLED

Pack (number of units)	1
Volume (dm ³)	175,403
Weight (g)	26 000,00

Product characteristics

Linkeo fix 19" cabinets

Fix side panels

- Delivered ready-assembled
- Depth 450 mm
- Capacity : 12 U
- Height : 625 mm
- Width : 600 mm
- Loading capacity : 36 kg

General characteristics

Linkeo 19" and 10" wall-mounting cabinets

- IP 20 - IK 08
- Equipped with:
 - 1 reversible door made of screen-printed safety glass and with integrated lock
 - 2 x 19" uprights with U marking and adjustable in depth
 - 3 pre-cut cable entries (top, bottom and rear). 1 brush for a cable entry. Top perforations for natural ventilation
 - panels with automatic grounding (ready assembled version)
 - earthing kit (flatpack version)
- Anthracite grey RAL 7016

Documentation

Catalogue pages & additional information

- [Description page \(p.784\)](#)
- [Technical page \(p.790\)](#)
- [Technical page \(p.791\)](#)

Installation & technical data

- F02824EN-00

Installation instructions & related documents

- [LE10110AA-01](#)

Environmental product profile

- [LGRP-01458-V01](#)

CAT. N° 6 462 02

Spare parts

CAT. NO.	DESCRIPTION	UNIT PRICE	MINIMUM ORDER QUANTITY
981080	SET OF 2 HINGES FOR LINKEO WALLMOUNTING CABINET		1
981082	LOCKING KIT (BARREL AND KEY) FOR LINKEO DOOR		1
981083	SET OF 2 KEYS (CODE 9473) FOR LINKEO RAL7016 DOOR AND SIDE PANELS		1
981086	LINKEO RAL7016 COMPLETE DOOR 12UX19" (MOUNTED, FLATPACK AND PIVOTING VERSION)		1

Spare Parts Guarantee

Does not affect the guarantee for the finished product.

Spare parts guaranteed against defects if exchanged within 2 weeks.