

CAT. N° 6 462 61



LINKEO FIX 19" CABINET WITH REMOVABLE SIDE PANELS - CAPACITY 9U - DIMENSIONS 471X600X600 MM - READY-ASSEMBLED

Pack (number of units)	1
Volume (dm ³)	90,112
Weight (g)	28 000,00

Product characteristics

Linkeo fix 19" cabinets

Removable side panels

- For easy access at the side of the cabinet
- Opening with a lock (same key as the door)
- Delivered flatpack
- Depth 600 mm
- Capacity: : 9 U
- Height: : 471 mm
- Width: : 600 mm
- Loading capacity: : 27 kg

General characteristics

Linkeo 19" and 10" wall-mounting cabinets

- IP 20 - IK 08
- Equipped with:
 - 1 reversible door made of screen-printed safety glass and with integrated lock
 - 2 x 19" uprights with U marking and adjustable in depth
 - 3 pre-cut cable entries (top, bottom and rear). 1 brush for a cable entry. Top perforations for natural ventilation
 - panels with automatic grounding (ready assembled version)
 - earthing kit (flatpack version)
- Anthracite grey RAL 7016

Documentation

Catalogue pages & additional information

- [Description page \(p.784\)](#)
- [Technical page \(p.790\)](#)
- [Technical page \(p.791\)](#)

Installation & technical data

- F02826EN-00

Installation instructions & related documents

- [LE10111AA-01](#)

Environmental product profile

- [LGRP-01458-V01](#)

CAT. N° 6 462 61

Spare parts

CAT. NO.	DESCRIPTION	UNIT PRICE	MINIMUM ORDER QUANTITY
981080	SET OF 2 HINGES FOR LINKEO WALLMOUNTING CABINET		1
981081	LOCKING KIT (BARREL AND KEY) FOR LINKEO SIDE PANELS (FLATPACK AND PIVOT VERSION)		1
981082	LOCKING KIT (BARREL AND KEY) FOR LINKEO DOOR		1
981083	SET OF 2 KEYS (CODE 9473) FOR LINKEO RAL7016 DOOR AND SIDE PANELS		1
981085	LINKEO RAL7016 COMPLETE DOOR 9UX19" (MOUNTED, FLATPACK AND PIVOTING VERSION)		1

Spare Parts Guarantee

Does not affect the guarantee for the finished product.

Spare parts guaranteed against defects if exchanged within 2 weeks.