

CAT. N° 6 462 63



LINKEO FIX 19" CABINET WITH REMOVABLE SIDE PANELS - CAPACITY 15U - DIMENSIONS 738X600X600 MM - READY-ASSEMBLED

Pack (number of units)	1
Volume (dm ³)	111,54
Weight (g)	32 000,00

Product characteristics

Linkeo fix 19" cabinets

Removable side panels


- For easy access at the side of the cabinet
- Opening with a lock (same key as the door)
- Delivered flatpack
- Depth 600 mm
- Capacity : 15 U
- Height : 738 mm
- Width : 600 mm
- Loading capacity : 45 kg

General characteristics

Linkeo 19" and 10" wall-mounting cabinets

- IP 20 - IK 08
- Equipped with:
 - 1 reversible door made of screen-printed safety glass and with integrated lock
 - 2 x 19" uprights with U marking and adjustable in depth
 - 3 pre-cut cable entries (top, bottom and rear). 1 brush for a cable entry. Top perforations for natural ventilation
 - panels with automatic grounding (ready assembled version)
 - earthing kit (flatpack version)
- Anthracite grey RAL 7016

Documentation

 **Catalogue pages & additional information**

- [Description page \(p.784\)](#)
- [Technical page \(p.790\)](#)
- [Technical page \(p.791\)](#)

 **Installation & technical data**

- [F02826EN-00](#)

 **Installation instructions & related documents**

- [LE10111AA-01](#)

 **Environmental product profile**

- [LGRP-01458-V01](#)

CAT. N° 6 462 63

Spare parts

CAT. NO.	DESCRIPTION	UNIT PRICE	MINIMUM ORDER QUANTITY
981080	SET OF 2 HINGES FOR LINKEO WALLMOUNTING CABINET		1
981081	LOCKING KIT (BARREL AND KEY) FOR LINKEO SIDE PANELS (FLATPACK AND PIVOT VERSION)		1
981082	LOCKING KIT (BARREL AND KEY) FOR LINKEO DOOR		1
981083	SET OF 2 KEYS (CODE 9473) FOR LINKEO RAL7016 DOOR AND SIDE PANELS		1
981087	LINKEO RAL7016 COMPLETE DOOR 15UX19" (MOUNTED, FLATPACK AND PIVOTING VERSION)		1

Spare Parts Guarantee

Does not affect the guarantee for the finished product.

Spare parts guaranteed against defects if exchanged within 2 weeks.