

CAT. N° 6 468 30



## 19" PDU LCS<sup>3</sup> - 1 U - 6 X 2P+E - FRENCH STANDARD - 16 A 1P MCB

Pack (number of units)	1
Volume (dm <sup>3</sup> )	3,233
Weight (g)	1 104,00

### Product characteristics

#### 19" Basic PDU with protection devices

- MCB and RCBO support with projecting edges to avoid accidental breakdown
- 3 m power supply cord with 16 A 2P+E French/German plug

#### French standard

- 6 outlets and a 16 A single pole Micro Circuit Breaker

### General characteristics

#### Legrand cabling system LCS<sup>3</sup> energy distribution - 1U Basic Power Distribution Units (PDU)

- To provide ~ electric power for IT equipment in 19" enclosures
- 230 V - 50/60 Hz power supply
- 1U aluminium profile
- End cap with metallic brackets and cable holder shape
- Quick fixing (no screws) on 19" fixing centers. Can also be installed vertically by reverting the brackets (no screws)
- 2P+E outlets:
  - C13 and C19 standard outlets are equipped with cord locking system to avoid any accidental disconnection. Universal solution compatible with all the cords (C14 plugs for C13 and C20 plugs for C19)
  - French, German and British standard outlets are equipped with safety shutters
  - French and German standard outlets are inclined at 55°
- Black modules (outlets and functions)

### Documentation



#### Catalogue pages & additional information

- [Selection chart \(p.725\)](#)
- [Description page \(p.772\)](#)
- [Technical page \(p.779\)](#)



#### Installation & technical data

- [S000093176EN-12](#)

## CAT. N° 6 468 30

## Spare parts

CAT. NO.	DESCRIPTION	UNIT PRICE	MINIMUM ORDER QUANTITY
980450	SET OF TWO 19 INCH BRACKETS		1
980452	TRANSPARENT COVER FOR MCB SUPPORT		1

**Spare Parts Guarantee**

Does not affect the guarantee for the finished product.

Spare parts guaranteed against defects if exchanged within 2 weeks.