

CAT. N° 6 468 36



19" PDU LCS³ - 1 U - 6 X 2P+E - GERMAN STANDARD - WITH SPD

Pack (number of units)	1
Volume (dm ³)	3,233
Weight (g)	1 037,00

Product characteristics

19" Basic PDU with surge protection

- Protect against mains overvoltages while keeping outlets energised
- With light indicators:
 - one LED (white) gives information whether the PDU is supplied with power or not
 - one LED (green) indicates when surge protection module is efficient or must be replaced
- Equipped with hotswappable surge protection module Cat.No 6 468 97: even when the module is being replaced, the PDU and its outlets are still powered on
- With switch
- 3 m power supply cord with 16 A 2P+E French/German plug
- 6 outlets - German standard

General characteristics

Legrand cabling system LCS³ energy distribution - 1U Basic Power Distribution Units (PDU)

- To provide ~ electric power for IT equipment in 19" enclosures
- 230 V - 50/60 Hz power supply
- 1U aluminium profile
- End cap with metallic brackets and cable holder shape
- Quick fixing (no screws) on 19" fixing centers. Can also be installed vertically by reverting the brackets (no screws)
- 2P+E outlets:
 - C13 and C19 standard outlets are equipped with cord locking system to avoid any accidental disconnection. Universal solution compatible with all the cords (C14 plugs for C13 and C20 plugs for C19)
 - French, German and British standard outlets are equipped with safety shutters
 - French and German standard outlets are inclined at 55°
- Black modules (outlets and functions)

Documentation

Catalogue pages & additional information

- [Selection chart \(p.725\)](#)
- [Description page \(p.772\)](#)
- [Technical page \(p.779\)](#)

Installation & technical data

- [S000093176EN-09](#)

Installation instructions & related documents

- [LE09269AA-03](#)

CAT. N° 6 468 36

Spare parts

CAT. NO.	DESCRIPTION	UNIT PRICE	MINIMUM ORDER QUANTITY
980450	SET OF TWO 19 INCH BRACKETS		1

Spare Parts Guarantee

Does not affect the guarantee for the finished product.

Spare parts guaranteed against defects if exchanged within 2 weeks.