

CAT. N° 6 468 41



19" PDU LCS³ - 1 U - 6 X 2P+E - GERMAN STANDARD - WITH AMMETER

Pack (number of units)	1
Volume (dm ³)	2,431
Weight (g)	998,00

Product characteristics

19" Basic PDU with ammeter

- Measure consumption to provide better installation management: balancing circuits, displaying available capacity, preventing overloads and power failures
- Measure total PDU current
- Rotating display to ensure a perfect reading whatever the PDU mounting direction is (horizontal, vertical with top or bottom power supply input)

German standard

- 3 m power supply cord with 16 A 2P+E French/German plug
- 6 outlets

General characteristics

Legrand cabling system LCS³ energy distribution - 1U Basic Power Distribution Units (PDU)

- To provide ~ electric power for IT equipment in 19" enclosures
- 230 V - 50/60 Hz power supply
- 1U aluminium profile
- End cap with metallic brackets and cable holder shape
- Quick fixing (no screws) on 19" fixing centers. Can also be installed vertically by reverting the brackets (no screws)
- 2P+E outlets:
 - C13 and C19 standard outlets are equipped with cord locking system to avoid any accidental disconnection. Universal solution compatible with all the cords (C14 plugs for C13 and C20 plugs for C19)
 - French, German and British standard outlets are equipped with safety shutters
 - French and German standard outlets are inclined at 55°
- Black modules (outlets and functions)

Documentation

Catalogue pages & additional information

- [Selection chart \(p.725\)](#)
- [Description page \(p.772\)](#)
- [Technical page \(p.779\)](#)

Installation instructions & related documents

- [LE09269AA-03](#)

CAT. N° 6 468 41

Spare parts

CAT. NO.	DESCRIPTION	UNIT PRICE	MINIMUM ORDER QUANTITY
980450	SET OF TWO 19 INCH BRACKETS		1

Spare Parts Guarantee

Does not affect the guarantee for the finished product.

Spare parts guaranteed against defects if exchanged within 2 weeks.