

CAT. N° 6 468 98



10" PDU LCS³ - 1 U - TO BE EQUIPPED - 8 MOSAIC MODULES

Pack (number of units)	1
Volume (dm ³)	1,614
Weight (g)	225,00

Product characteristics

Equipment for 10" cabinets

10" Power Distribution Units (PDU)

- 230 V - 50/60 Hz power supply
- 1 U aluminium profile
- End cap with metallic brackets and cable holder shape
- Quick fixing (no screws) on 19" uprights
- With shutters and inclined at 55°
- PDU 10
- Capacity: 8 Mosaic modules

General characteristics

Linkeo 19" and 10" wall-mounting cabinets

- IP 20 - IK 08
- Equipped with:
 - 1 reversible door made of screen-printed safety glass and with integrated lock
 - 2 x 19" uprights with U marking and adjustable in depth
 - 3 pre-cut cable entries (top, bottom and rear). 1 brush for a cable entry. Top perforations for natural ventilation
 - panels with automatic grounding (ready assembled version)
 - earthing kit (flatpack version)
- Anthracite grey RAL 7016

Documentation



Catalogue pages & additional information

- [Description page \(p.774\)](#)
- [Description page \(p.784\)](#)
- [Technical page \(p.790\)](#)
- [Technical page \(p.791\)](#)



Installation & technical data

- [S000093176EN-12](#)

CAT. N° 6 468 98

Spare parts

CAT. NO.	DESCRIPTION	UNIT PRICE	MINIMUM ORDER QUANTITY
980450	SET OF TWO 19 INCH BRACKETS		1

Spare Parts Guarantee

Does not affect the guarantee for the finished product.

Spare parts guaranteed against defects if exchanged within 2 weeks.