

REF . 6 514 16

**RIGID CONDUIT - WITH COUPLING - SHOCK RESISTANCE
2 JOULES - Ø EXT. 16 MM**

Emballage (nombre number of units)	30
Volume (dm ³)	13
Poids (g)	2 800,00

Caractéristiques du produit**Medium impact rigid conduits with integrated coupling**

- PVC without Pb, Sn, Cd (RoHS compliant)
- Non flame propagating
- Surface-mounting or flush-mounting
- Suitable for prefabricated concrete. Conforming to European standard: EN/IEC 61386-21
- Crush resistance: 750 Newtons. Impact resistance: 2 joules at - 5 °C
- Min operating t°: - 5 °C ; Max operating t°: + 60 °C
- IK 07
- Can be used outside
- Supplied wrapped in film. Light grey (RAL 7035)
- Length of tubes: 3 m
- Ø exterior : : 16 mm
- Ø interior : : 13 mm
- thickness : : 1.50 mm

Caractéristiques générales**Rigid conduits****Documentation associée****Catalogue pages & additional information**

- [Description page \(p.624\)](#)

**Installation & technical data**

- [F01719EN-02](#)